

DX1001-T

The DX modular housing arrangement offers a flexible and space conscious solution to integrate our innovative DXO Cartridge in to both new and existing systems. The Delta-Xero system can be configured up to 12 cartridges in parallel as a single unit in a compact and easily maintainable layout.

The unit can be supplied with a number of standard options to provide an effective fluid conditioning and monitoring package to suit the majority of systems. The flexibility of the unit allows tailoring to customer's specific requirements.





\Box	X1	\sim	-	
	P. 311	 0 M		

Drive Input	Electric or Pneumatic		
Connection Ports	3/8"BSP In & Out		
Flow Indicator	Visual		
Suggested System Volume	Up to 4500ltrs @ 32cSt		
Particulate Removal	From 0,1 μ		
Weight	20 kg		
Dimensions	H 674 mm x D 300 mm x L 550 mm		
Material	SS316		
DXO Cartridge QTY	1		


Flow Rate varies depending on viscosity, pressure and temperature


Approx	32 cSt	46 cSt	68 cSt	100 cSt	220 cSt	320 cSt	460 cSt
flow at 2.7	1.25 l/min	1.0 l/min	0.8 l/min	0.6 l/min	0.4 l/min	0.2 l/min	0.1 l/min
bar:					·		
Oil Volume	4500ltrs	3500ltrs	3000ltrs	2400ltrs	1800ltrs	800ltrs	⊿ooltrs





DX1001-T

General Arrangement + Schematic









Cartridge Data: DXO

Contaminated weight:	Up to 4.5kg per DXO		
Water holding capacity, free and bound:	Approx. 2600ml		
Material insert:	PP Cellulose mix		



